



Model	Description
PX-1000	PDU Metered: Meter the PDU for a wealth of power data. The only PDU in the market providing branch circuit metering and circuit breaker trip status.
PX2-1495V-E2	1PH, 208V, 30A (24A rated), 24 outlets: 18 x locking IEC C-13, 6 x locking IEC C-19, plug: NEMA L6-30P (bottom/bottom feed), 5.0kVA, unit metered, Zero U Vertical PDU, Ethernet, serial, USB-A, USB-B and sensor connections
PX2-1497V	1PH, 208V AC, 30A (24A rated), 24 outlets: 20 x IEC C-13, 4 x IEC C-19, plug: NEMA L6-30P (bottom/bottom feed), 5.0kVA, Zero U vertical PDU, Ethernet, serial, USB-A, USB-B and sensor connections
PX2-1508	3PH, 208V AC, 20A (16A/PH rated), 24 outlets: IEC C-13, plug: NEMA L21-20P (Wye), 5.8kVA, Zero U vertical PDU, Ethernet, serial, USB-A, USB-B and sensor connections
PX2-1525V-E2	3PH, 208V, 30A (24A/PH rated), 24 outlets: 18 x locking IEC C-13, 6 x locking IEC C-19, plug: NEMA L15-30P (delta, bottom/bottom feed), 8.6kVA, unit metered, Zero U Vertical PDU, Ethernet, serial, USB-A, USB-B and sensor connections
PX2-1551	3PH, 208V AC, 60A (48A/PH rated), 24 outlets: 12 x IEC C-13, 12 x IEC C-19, plug: IEC60309 60A 3P (Delta, bottom feed), 17.3kVA, unit metered, Zero U vertical PDU, SecureLock ready, Ethernet, serial, USB-A, USB-B and sensor connections
PX2-1551V-E2V2	3PH, 208V, 60A (48A/PH rated), 24 outlets: 12 x locking IEC C-13, 12 x locking IEC C-19, plug: IEC 60309 60A 3P (delta, bottom/bottom feed), 17.3kVA, unit metered, Zero U Vertical PDU, Ethernet, serial, USB-A, USB-B and sensor connections
PX2-1802	1PH, 120V AC, 20A (16A rated), 24 outlets: NEMA 5-20R, plug: NEMA 5-20P, 1.9kVA, Zero U vertical PDU, Ethernet, serial, USB-A, USB-B and sensor connections
PX-2000	PDU Metered, Outlet Switched: Meter the PDU and remotely switch outlets
PX2-2180R	1PH, 208V AC, 20A (16A/PH rated), 8 outlets: IEC C-13, plug: NEMA L6-20P, 3.3kVA, 1U horizontal PDU, Ethernet, serial, USB-A, USB-B and sensor connections
PX2-2706	3PH, 208V, 50A (35A/PH rated), 36 outlets: 36 x IEC C-13, plug: CS8365C (bottom feed), 14.4kVA, unit metered, Zero U Vertical PDU, SecureLock ready, Ethernet, serial, USB-A, USB-B and sensor connections
PX2-2735	3PH, 208V AC, 20A (16A/PH rated), 36 outlets: 24 x IEC C-13, 12 x IEC C-19, plug: NEMA L21-20P (Wye, bottom feed), 5.8kVA, unit metered/switched, Zero U vertical PDU, SecureLock ready, Ethernet, serial, USB-A, USB-B and sensor connections
PX2-2776	3PH, 208V AC, 35A (35A/PH rated), 48 outlets: IEC C-13, plug: CS8365C (Delta, bottom feed), 12.6kVA, unit metered/switched, Zero U vertical PDU, SecureLock ready, Ethernet, serial, USB-A, USB-B and sensor connections
PX-3000	Inline Metered: Meter circuits running directly to devices
PX-3220	1PH, 100-240V AC, 16-32A, 2 lines, input type: 2 x AC terminal, output type: 2 x AC terminal, 1U, Ethernet, serial, and sensor connections
PX-3420	1PH, 100-240V AC, 16-32A, 4 lines, input type: 4 x AC terminal, output type: 4 x AC terminal, 1U, Ethernet, serial and sensor connections
PX-4000	Outlet Metered: Meter individual outlets to monitor individual IT devices
PX2-4660	3PH, 208V AC, 30A (24A/PH rated), 30 outlets: 21 x IEC C-13, 6 x IEC C-19, 3 x NEMA 5-20R, plug: NEMA L21-30P (Wye), 8.6kVA, Zero U vertical PDU, Ethernet, serial, USB-A, USB-B and sensor connections
PX2-4913U-A1K3	3PH Wye, 400V AC, 30A (24A/PH rated), 18 outlets: 6 x IEC C-13, 12 x IEC C-19, plug: NEMA L22-30P 3P+N+PE, 16.6kVA, Zero U vertical PDU, Ethernet, serial, USB-A, USB-B and sensor connections
PX-4198-C1	1PH, 208V AC, 30A (24A rated), 8 outlets: 6 x IEC C-13, 2 x IEC C-19, plug: NEMA L6-30P, 5.0kVA, 1U horizontal PDU, Ethernet, serial and sensor connections
PX-4316	3PH, 208V AC, 50A (40A/PH rated), 12 outlets: IEC C-19, plug: CS8365C (Delta), 14.4kVA, Zero U vertical PDU, Ethernet, serial and sensor connections
PX-4386	1PH, 208V AC, 30A (24A rated), 16 outlets: IEC C-13, plug: NEMA L6-30P, 5.0kVA, Zero U vertical PDU, Ethernet, serial and sensor connections
PX-4524	3PH, 208V AC, 30A (24A/PH rated), 24 outlets: 18 x IEC C-13, 6 x IEC C-19, plug: NEMA L21-30P (Wye), 8.6kVA, Zero U vertical PDU, Ethernet, serial and sensor connections
PX-4532	3PH, 208V AC, 50A (35A/PH rated), 24 outlets: IEC C-13, plug: CS8365C (Delta), 12.6kVA, Zero U vertical PDU, Ethernet, serial and sensor connections
PX-5000	Outlet Metered, Outlet Switched: Meter and switch individual outlets to monitor and control IT devices
PX2-5146R	1PH, 120V AC, 20A (16A rated), 8 outlets: NEMA 5-20R, plug: NEMA 5-20P, 1.9kVA, outlet metered/switched, 1U horizontal PDU, Ethernet, serial, USB-A, USB-B and sensor connections
PX2-5200R	1PH, 208V AC, 30A (24A rated), 8 outlets: IEC C-13, plug: NEMA L6-30P, 5.0kVA, 1U horizontal PDU, Ethernet, serial, USB-A, USB-B and sensor connections
PX2-5630	3PH, 400V AC, 30A (24A/PH rated), 24 outlets: 18 x IEC C-13, 6 x IEC C-19, plug: NEMA L22-30P (Wye), 16.6kVA, Zero U vertical PDU, Ethernet, serial, USB-A, USB-B and sensor connections
PX2-5649	3PH, 208V AC, 30A (24A/PH rated), 30 outlets: IEC C-13, plug: NEMA L21-30P (Wye), 8.6kVA, Zero U vertical PDU, Ethernet, serial, USB-A, USB-B and sensor connections
PX2-5660-E2	3PH, 208V AC, 30A (24A/PH rated), 30 outlets: 21 x locking IEC C-13, 6 x locking IEC C-19, 3 x NEMA 5-20R, plug: NEMA L21-30P (Wye), 8.6kVA, Zero U vertical PDU, Ethernet, serial, USB-A, USB-B and sensor connections
PX2-5704I2U-N1A1	3PH, 400V AC, 30A (24A/PH rated), 36 outlets: IEC C-13, plug: NEMA L22-30P (Wye, top/top feed), 16.6kVA, Zero U vertical PDU, Ethernet, serial, USB-A, USB-B and sensor connections
PX2-5941V-V2	3PH, 208V AC, 100A (80A/PH rated), 18 outlets: IEC C-19, plug: IEC60309 100A 3P (Delta, bottom/bottom feed), 28.8kVA, Zero U vertical PDU, Ethernet, serial, USB-A, USB-B and sensor connections

PX2-5980I2U-N1A1	3PH, 400V AC, 40A (40A/PH rated), 24 outlets: 6 x IEC C-13, 18 x IEC C-19, plug: IEC 60309 40A 3PY (Wye, top/top feed), 27.7kVA, Zero U vertical PDU, Ethernet, serial, USB-A, USB-B and sensor connections
PX-5198	1PH, 208V AC, 30A (24A rated), 8 outlets: 6 x IEC C-13, 2 x IEC C-19, plug: NEMA L6-30P, 5.0kVA, 1U horizontal PDU, Ethernet, serial and sensor connections
PX-5301	3PH, 208V AC, 60A (48A/PH rated), 12 outlets: IEC C-19, plug: IEC 60309 60A 3P+PE (Delta), 17.3kVA, 2U horizontal PDU, Ethernet, serial and sensor connections
PX-5464T	1PH, 208V AC, 30A (24A rated), 20 outlets: 16 x IEC C-13, 4 x IEC C-19, plug: NEMA L6-30P, 5.0kVA (top feed), Zero U vertical PDU, Ethernet, serial and sensor connections
PX-5510	3PH, 208V AC, 20A (16A/PH rated), 24 outlets: 21 x IEC C-13, 3 x IEC C-19, plug: NEMA L21-20P (Wye), 5.8kVA, Zero U vertical PDU, Ethernet, serial and sensor connections
PX-5530	3PH Wye, 400V AC, 32A, 24 outlets: 21 x IEC C-13, 3 x IEC C-19, plug: IEC 60309 32A 3P+N+PE, 22.2kVA, Zero U vertical PDU, Ethernet, serial and sensor connections
PX-5534	3PH, 208V AC, 50A (35A/PH rated), 24 outlets: 21 x IEC C-13, 3 x IEC C-19, plug: CS8365C (Delta), 12.6kVA, Zero U vertical PDU, Ethernet, serial and sensor connections
PX2-5535	3PH, 208V AC, 50A (35A/PH rated), 24 outlets: 18 x IEC C-13, 6 x IEC C-19, plug: CS8365C (Delta, bottom feed), 12.6kVA, outlet metered/switched, Zero U vertical PDU, SecureLock ready, Ethernet, serial, USB-A, USB-B and sensor connections
PX-5550	3PH, 400V AC, 30A (24A/PH rated), 24 outlets: 12 x IEC C-13, 12 x IEC C-19, plug: NEMA L22-30P (Wye), 16.6kVA, Zero U vertical PDU, Ethernet, serial and sensor connections
PX-5551	3PH Delta, 208V AC, 60A (48A/PH rated), 24 outlets: 12 x IEC C-13, 12 x IEC C-19, plug: IEC 60309 60A 3P+PE, 17.3kVA, Zero U vertical PDU, Ethernet, serial and sensor connections
PX-5630	3PH, 400V AC, 30A (24A/PH rated), 24 outlets: 18 x IEC C-13, 6 x IEC C-19, plug: NEMA L22-30P (Wye), 16.6kVA, Zero U vertical PDU, Ethernet, serial and sensor connections
PX-5633	3PH, 400V AC, 30A (24A/PH rated), 24 outlets: 21 x IEC C-13, 3 x IEC C-19, plug: NEMA L22-30P (Wye), 16.6kVA, Zero U vertical PDU, Ethernet, serial and sensor connections
PX-5652	3PH, 120/208V AC, 30A (24A/PH rated), 24 outlets: 18 x IEC C-13, 3 x IEC C-19, 3 x NEMA 5-20R, plug: NEMA L21-30P (Wye), 8.6kVA, Zero U vertical PDU, Ethernet, serial and sensor connections
PX-5810	1PH, 208V AC, 30A (24A rated), 6 outlets: NEMA L6-20R, plug: NEMA L6-30P, 5.0kVA, 2U horizontal PDU, Ethernet, serial and sensor connections
PX-5902T	3PH, 208V, 30A (24A/PH rated), 18 outlets: 12 x IEC C-13, 6 x IEC C-19, plug: NEMA L21-30P (Wye, top feed), 8.6kVA, Zero U vertical PDU, Ethernet, serial and sensor connections
DPXR20-20	1PH, 120V AC, 20A (16A rated), 20 outlets: NEMA 5-15R, plug: NEMA 5-20P, 1.9kVA, outlet metered/switched, 2U horizontal PDU, Ethernet, serial and sensor connections
DPXR20-20L	1PH, 120V AC, 20A (16A rated), 20 outlets: NEMA 5-15R, plug: NEMA L5-20P, 1.9kVA, outlet metered/switched, 2U horizontal PDU, Ethernet, serial and sensor connections
DPXR20-30L	1PH, 120V AC, 30A (24A rated), 20 outlets: NEMA 5-15R, plug: NEMA L5-30P, 2.9kVA, outlet metered/switched, 2U horizontal PDU, Ethernet, serial and sensor connections
DPXS12-30L	1PH, 120V AC, 30A (24A rated), 12 outlets: NEMA 5-15R, plug: NEMA L5-30P (bottom feed), 2.9kVA, outlet metered/switched, Zero U vertical PDU, Ethernet, serial and sensor connections
DPXS20-20L	1PH, 120V AC, 20A (16A rated), 20 outlets: NEMA 5-15R, plug: NEMA L5-20P (bottom feed), 1.9kVA, outlet metered/switched, Zero U vertical PDU, Ethernet, serial and sensor connections
DPXS20-30L	1PH, 120V AC, 30A (24A rated), 20 outlets: NEMA 5-15R, plug: NEMA L5-30P (bottom feed), 2.9kVA, outlet metered/switched, Zero U vertical PDU, Ethernet, serial and sensor connections
DPXS20A-20L6	1PH, 208V AC, 20A (16A rated), 20 outlets: IEC C-13, plug: NEMA L6-20P (bottom feed), 3.3kVA, outlet metered/switched, Zero U vertical PDU, SecureLock ready, Ethernet, serial and sensor connections

Raritan is a proven innovator of power management solutions, DCIM software, and KVM-over-IP for data centers of all sizes. Based in Somerset, NJ, Raritan has a global presence across 38 offices, serving 76 countries and 50,000 locations worldwide. Raritan's award-winning hardware and software solutions increase energy efficiency, improve reliability, and raise productivity. For more information, please visit www.raritan.com or call 800-724-8090.

2014 Raritan Inc. All rights reserved. Raritan®, Know more. Manage smarter.™ are registered trademarks or trademarks of Raritan Inc. or its wholly-owned subsidiaries. All others are registered trademarks or trademarks of their respective owners.