

INTELLIGENT POWER DISTRIBUTION UNITS

Product	Description
DPXS12A-32	Outlet Metered & Outlet Switched PDU - 12 Outlets (12 x IEC C13), Single Phase, 32A, 7.36 kVA, 230V AC, Zero U, Black
PX-4530	Outlet Switched PDU - 24 Outlets: (21 x IEC C13, 3 x IEC C19), 3 Phase Wye, 400V AC, 32A, 22.2kVA, Zero U Vertical, Black
PX-5297	Outlet Metered & Outlet Switched - 12 Outlets (8 x IEC C13, 4 x IEC C19), Single Phase, 230V AC, 32A, 7.36kVA, Zero U Vertical, Black
PX-5315	Outlet Metered & Outlet Switched - 12 Outlets (12 x IEC C13), 3 Phase Wye, 400V AC, 16A, 11.1kVA, Zero U Vertical, Black
PX-5397	Outlet Metered & Outlet Switched - 16 Outlets (12 x IEC C13, 4 x IEC C19), Single Phase, 230V AC, 32A, 7.36kVA, Zero U Vertical, Black
PX-5469T	Outlet Metered & Outlet Switched - 20 outlets (16 x IEC C13, 4 x IEC C19), Single Phase, 230V AC, 32A, 7.36kVA, Zero U Vertical, Top Fed, Black
PX-5917	Outlet Metered & Outlet Switched - 24 outlets (12 x IEC C13, 12 x IEC C19), 3 Phase Wye, 400V AC, 32A, 22.2kVA, Zero U Vertical, Black

INLINE POWER METERING

Product	Description
PX2-3170	Inline Meter - 3 Phase Wye, 380-415V AC, 32/30A (32A/PH rated), 1 line, Input: 1 x AC Terminal, Outlet: 1 x AC Terminal, Zero U
PX-3220	Inline Meter - Single Phase, 100-240V AC, 16-32A, 2 Lines, Input: 2 x AC Terminal, Output: 2 x AC Terminal, USB-A, USB-B, 1U
PX2-3230	Inline Meter - Single Phase, 100-240V AC, 63A, 2 Lines, Input: 2 x AC Terminal, Output: 2 x AC Terminal, USB-A, USB-B, 1U

Raritan is a proven innovator of power management solutions, DCIM software, and KVM-over-IP for data centers of all sizes. Based in Somerset, NJ, Raritan has a global presence across 38 offices, serving 76 countries and 50,000 locations worldwide. Raritan's award-winning hardware and software solutions increase energy efficiency, improve reliability, and raise productivity. For more information, please visit www.raritan.eu or call +31 (0)10-284 40 40.

2015 Raritan Inc. All rights reserved. Raritan®, Know more. Manage smarter.™ are registered trademarks or trademarks of Raritan Inc. or its wholly-owned subsidiaries. All others are registered trademarks or trademarks of their respective owners.

ACCESS PRODUCTS

Product	Description
DKX2-132	Dominion KX II - 32 Port KVM-over-IP Switch, 1 Remote User, 1 Local User, Virtual Media, Dual Power
DKX2-832	Dominion KX II - 32 Port KVM-over-IP Switch, 8 Remote Users, 1 Local User + Extended Local Port, Virtual Media, Dual Power
P2-UMT832S	Paragon II - Cat5 Matrix Stacking Switch 0 User, 32 Expansion Ports for Stacking with P2-UMT832M Unit
P2-USTIP1	Paragon II IP Enabled User Station, 1 User Model
P2-USTIP2	Paragon II IP Enabled User Station, 2 User Model
T1700	17" LCD KVM Drawer, 1U, Choice of Language Keyboards

ASSET TRACKING

Product	Description
AMS-45	Asset Management Sensor Kit for 45U Height Rack. 1 Connector and 1 RGB LED per U Space
AMS-47	Asset Management Sensor Kit for 47U Height Rack. 1 Connector and 1 RGB LED per U Space

Raritan is a proven innovator of power management solutions, DCIM software, and KVM-over-IP for data centers of all sizes. Based in Somerset, NJ, Raritan has a global presence across 38 offices, serving 76 countries and 50,000 locations worldwide. Raritan's award-winning hardware and software solutions increase energy efficiency, improve reliability, and raise productivity. For more information, please visit www.raritan.eu or call +31 (0)10-284 40 40.

2015 Raritan Inc. All rights reserved. Raritan®, Know more. Manage smarter.™ are registered trademarks or trademarks of Raritan Inc. or its wholly-owned subsidiaries. All others are registered trademarks or trademarks of their respective owners.